Eaton E50KL539

Catalog Number: E50KL539

Limit Switch Lever, E50, Accessory, Adjustable ball bearing roller, Used with side rotary, Stainless steel

General specifications

Product Name

Catalog Number

Eaton E50 NEMA heavy duty plug-in limit E50KL539

switch operator

UPC

782113361871

Product Length/Depth

Product Height 0.84 in

4.6 in

Product Weight

0.45 lb

Product Width

0.15 lb

0.69 in

Compliances

RoHS Compliant

Warranty
1 year

Certifications

UL Listed

CSA Certified

CE





default Taxonomy Attribute Label

Type

Accessory

Used with

Used with side rotary

Actuator

Adjustable ball bearing roller

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,

NEMA 6P, NEMA 13, IP67

Material

Stainless steel

Resources

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E50KL539



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia