Eaton E50KL544

Catalog Number: E50KL544

Limit Switch Lever, E50, Accessory, Fork lever both rollers on one side, Used with side rotary, Metal

General specifications



Product Name Catalog Number

Eaton E50 NEMA heavy duty plug-in limit E50KL544

switch operator

UPC

782113308708

Product Length/Depth

2.87 in

Product Height

0.62 in

Product Width

Product Weight

1.92 in

0.15 lb

Warranty

Compliances

1 year

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE



default Taxonomy Attribute Label

Type

Accessory

Used with

Used with side rotary

Actuator

Fork lever both rollers on one side

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 13, IP67

Material

Metal

Resources

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E50KL544



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia