

# Eaton E50KL599

Catalog Number: E50KL599

Limit Switch Operator, E50, Accessory, Adjustable roller, 0.5x0.48 in, 1.90 in-oz min. return, Used with side rotary, Nylatron

## General specifications



Product Name Catalog Number

Eaton E50 NEMA heavy duty plug-in limit E50KL599  
switch operator

UPC

782113302195

Product Length/Depth

4.6 in

Product Height

1.02 in

Product Width

0.75 in

Product Weight

0.15 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE



Powering Business Worldwide

**Type**

Accessory

**Used with**

Used with side rotary

**Actuator**

Adjustable roller

**Torque rating**

1.90 in-oz min return

**Series**

E50

**Operating temperature - max**

200 °F

**Operating temperature - min**

10 °F

**Environmental rating**NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67**Material**

Nylatron

**Size**

0.5 x 0.48 in

**Catalogs**[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E50KL599](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)