

Eaton E50NN1

Catalog Number: E50NN1

Eaton Special Purpose Limit Switch, E50 Heavy Duty Plug In, Neutral position 5° travel, Screw Terminals, 10A at 12 Vac, 1A at 125 Vdc, 2NO-2NC, 14° to 201°F (-10° to 94°C)



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50NN1
	UPC
	782113290706
Product Length/Depth	Product Height
4.22 in	2.46 in
Product Width	Product Weight
1.54 in	0.41 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Contact Rating

10A at 12 Vac, 1A at 125 Vdc

Enclosure material

Die cast zinc

Connection

Screw terminal

Contact configuration

2 NO-2 NC

Series

E50 heavy duty plug in

Switch type

Neutral position 5 ° travel

Operating temperature - max

201 °F

Operating temperature - min

14 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Maximum AC current

10 A

Maximum DC current

1 A

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50NN1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)