



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50NN1SPL E50NN19 W/ E50DN19Y1 Head Cold Temp/SS Steel

Eaton Corp

Catalog Number	E50NN1SPL
Manufacturer	Eaton Corp
Description	Heavy-Duty Plug-In Switch, E50 Series, 2NO-2NC Pole Throw Configuration, 10 A @ 12 V Ac; 1 A @ 125 V DC, 12 V Ac; 125 V DC, Die Cast Zinc (Enclosure) Material, Screw Terminal, +14 °F Operating Temperature, +201 °F Operating Temperature, 3 In Overall Width, 4.5 In Overall Depth, 6.5 In Overall Height, Chemical Resistant, 1 LB
Weight per unit	1.0 (lbs/each)
Product Category	Heavy Duty Limit Switches

Features

connection	Screw Terminal
dimensions	3.0000 IN X 4.5000 IN X 6.5000 IN

Descriptions

Description	E50NN19 W/ E50DN19Y1 HEAD COLD TEMP/SS STEEL
extra long description	ETN E50NN1SPL E50NN19 W/STAINLESS S

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113761114
UPC	782113761114

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other Ind Facilities & Factories - Industrial Facilities/Factories - Other
Operating Temperature	14
standard	UL Listed