

Limit Switch Receptacle

E50RA

UPC:782113290720

Dimensions:

- **Height:** 1.06 IN
- **Length:** 2.92 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Mounting:** Front, rear
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Number Of Poles:** Single-pole
- **Operating Temperature:** -40° to 250°F (-40° to 121°C)
- **Series:** E50 Heavy Duty Plug In
- **Switch Type:** Gravity return

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50RA](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data