



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50SA E50 Switch Body 1NO-1NC W/O Indicating Light

Eaton Corp

Catalog Number	E50SA
Manufacturer	Eaton Corp
Description	Limit Switch Body, E50 Heavy Duty Plug In Series, 1NO-1NC Contact Configuration, 10 A (Maximum AC); 1 A (Maximum DC), 12 V AC; 125 V DC, 1 Pole, Die Cast Zinc (Enclosure) Housing Material, -40 to +250 °F, 4.5 In Overall Length, 3.25 In Overall Width, 1.75 In Overall Depth, 0.4100 LB/Ea
Weight per unit	0.4100 (lbs/each)
Product Category	Limit Switch Bodies

Features

Contact Rating	10A at 12 Vac, 1A at 125 Vdc
dimensions	4.5000 IN X 3.2500 IN X 1.7500 IN
Poles	1

Descriptions

Description	E50 SWITCH BODY 1NO-1NC W/O INDICATING LIGHT
extra long description	ETN E50SA LIMIT SWITCH BODY, 1NO/1NC

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290676
UPC	782113290676

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	0.41

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - OtherWater and Wastewater Systems - Water and Wastewater Systems - OtherStationary Mach Equip In Factory - Machine Tools: CuttingStationary Mach Equip In Factory - Machine Tools: Forming
Operating Temperature	-40
standard	CSA Certified, UL Recognized, RoHS Compliant