

Eaton E50SA6P

Catalog Number: E50SA6P

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, 10A at 240Vac, 1A at 250Vdc, SOOW-J, 1NO-1NC, 96Foot, Die cast zinc, NEMA 1,3,3S,4,4X,6,6P,13,IP67,IP69K,10A,1A,-40° to 250°F (-40° to 121°C), E50 Heavy Duty Factory Sealed 6P+

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50SA6P
	UPC
	782113137049
Product Length/Depth	Product Height
3.63 in	2.46 in
Product Width	Product Weight
1.54 in	2.1 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Recognized	
CSA Certified	

defaultTaxonomyAttributeLabel

Contact Rating

10A at 240 Vac, 1A at 250 Vdc

Cable type

SOOW-A

Enclosure material

Die cast zinc

Cord length

96 ft

Contact configuration

1 NO-1 NC

Series

E50 heavy duty factory sealed 6P+

Operating temperature - max

250 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Maximum AC current

10 A

Maximum DC current

1 A

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50SA6P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia