

# Eaton E51DS5

Catalog Number: E51DS5

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.94 in range, Side Sensing, Unshielded, Standard frequency

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton E51 NEMA limit switch inductive proximity sensor	E51DS5
	UPC
	782113358949
<b>Product Length/Depth</b>	<b>Product Height</b>
1.38 in	1.51 in
<b>Product Width</b>	<b>Product Weight</b>
1.51 in	0.1 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

Actuator function

Unshielded

Frequency rating

Standard

Enclosure material

Plastic

Series

E51

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,  
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51DS5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)