



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E51RA Ind Prox Receptacle Only

Eaton Corp

Catalog Number	E51RA
Manufacturer	Eaton Corp
Description	Eaton E51 Nema Limit Switch Inductive Proximity Sensor, Assembled Inductive Proximity Fiber Optic Sensor, E51, Screw Terminals, 2-Wire, 20-264 Vac/DC
Weight per unit	0.4500 (lbs/each)
Product Category	Sensor Accessories

Features

connection	Screw Terminal
dimensions	2.9200 IN X 1.5400 IN X 1.0600 IN
Material	Die Cast Zinc

Descriptions

Description	IND PROX RECEPTACLE ONLY
extra long description	ETN E51RA IND PROX RECEPTACLE ONLY
Features	Eaton's E51 limit switch style modular sensors are available in thru-beam, reflex, polarized reflex, diffuse reflective and fiber optic sensing modes to solve a wide variety of sensing applications. Modular, plug-in components are easy to maintain, meaning less downtime and reduced inventory. Choose between 2-wire sensors with AC/DC operation and 4-wire sensors in either AC or DC styles. Connection options include terminal, mini-connector and various lengths of cable. Sensors can be ordered in component fo
Long Description	Eaton E51 NEMA limit switch inductive proximity sensor, Assembled Inductive Proximity Fiber Optic Sensor, E51, Screw Terminals, 2-wire, 20-264 Vac/dc
Product Type	Ind Prox Receptacle Only

Manufacturer Information

Brand	Eaton
GTIN	00782113884844
Manufacturers Part Number	E51RA
UPC	782113884844

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Limit switch inductive proximity sensor

Packaging

Carton	1
Weight Per each	0.45



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
Operating Temperature	-13
standard	UL Listed, CSA Certified