



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E55BLT1C Ind Prox Limit Switch Style 2WAC - Has 5 Way Head

Eaton Corp

Catalog Number	E55BLT1C
Manufacturer	Eaton Corp
Description	Inductive Proximity Sensor, No or NC Pole Throw Configuration, 15 MM Detecting Distance, 35 to 250 V, 400 Ma @ 250 V, 25 HZ, Screw Terminal;Terminal Wiring Connection, Led Indicator, PBT Resin (Enclosure) Material, -13 °F Operating Temperature, +158 °F Operating Temperature, 4.64 In Overall Length, 0.63 LB
Weight per unit	0.6300 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

connection	Screw Terminal
dimensions	4.6400 IN X 1.5700 IN X 1.5700 IN

Descriptions

Description	IND PROX LIMIT SWITCH STYLE 2WAC - HAS 5 WAY HEAD
extra long description	ETN E55BLT1C INDUCTIVE PROX,2WAC

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113134109
UPC	782113134109

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Photoelectric Sensor

Packaging

Carton	1
Weight Per each	0.63

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Car Wash
environmental conditions	NEMA 4, NEMA 4X, NEMA 6, NEMA 12, NEMA 13, IP67
standard	CE,CE Marked,RoHS Compliant