

# Eaton E57LAL12A2E

Catalog Number: E57LAL12A2E

Premium+ Inductive Proximity Sensor, E57, Straight, Unshielded, 360° viewable LED, 6.6 ft, 250 mA at 250V, <3% sensing range, PVC, 2-wire AC, NO, 20-250V

## General specifications



Product Name	Eaton E57 inductive proximity sensor	Catalog Number	E57LAL12A2E
UPC	782113742953	Product Length/Depth	2.87 in
Product Height	0.47 in	Product Width	0.47 in
Product Weight	0.7 lb	Warranty	1 year
Compliances	CE Marked	Certifications	UL Listed CSA Certified

## defaultTaxonomyAttributeLabel

### Type

E57

### Contact Rating

250 mA at 250V

### Actuator function

Unshielded

### Cable type

Polyvinyl Chloride (PVC)

### Accuracy

< 3% sensing range

### Enclosure material

303 stainless steel

### Contact configuration

2-wire AC, NO

### Series

E57

### Environmental rating

NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13,  
IP67, IP69K

### Temperature rating

-13 to 158 °F

### Cord length

79.2 ft

### Operating temperature - max

158 °F

### Operating temperature - min

-13 °F

### Maximum AC current

250 mA

### Input voltage

20-250 V

### LED indicator

360 ° viewable LED

## Resources

### Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

### Multimedia

[We make what matters](#)

### Specifications and datasheets

[Eaton Specification Sheet - E57LAL12A2E](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)