

Eaton E57LAL18T110S3

Catalog Number: E57LAL18T110S3

Inductive Proximity Sensor, E57, Straight, Shielded, 360° viewable LED, Cable, 9.8 ft, 500 mA at 6-30 Vdc, <1% sensing range, PVC, NO NPN open collector, 6-48 Vdc

General specifications



Product Name	Catalog Number
Eaton E57 inductive proximity sensor	E57LAL18T110S3
UPC	Product Length/Depth
782113790497	2.54 in
Product Height	Product Width
0.71 in	0.71 in
Product Weight	Warranty
0.3 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

Type

Inductive Proximity Sensor

Contact Rating

500 mA at 6-30 Vdc

Actuator function

Shielded

Cable type

Polyvinyl Chloride (PVC)

Accuracy

< 1% sensing range

Enclosure material

303 stainless steel

Connection

Cable

Contact configuration

NO NPN open collector

Series

E57

Environmental rating

NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K

Cord length

117.6 ft

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Maximum DC current

500 mA

Input voltage

6-48 Vdc

LED indicator

360 ° viewable LED

Protection

Auto reset

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Eaton's Volume 8—Sensing Solutions

Multimedia

We make what matters

Specifications and datasheets

Eaton Specification Sheet - E57LAL18T110S3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)