



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57LBL18A2E 8MM Range 20-250 2W Unshield Sensor *Eaton Corp*

Catalog Number	E57LBL18A2E
Manufacturer	Eaton Corp
Description	
Weight per unit	0.7000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

Accuracy	<3% sensing range
dimensions	66.0400millimetreX18.0340millimetreX18.0340millimetre

Descriptions

Description	8MM RANGE 20-250 2W UNSHIELD SENSOR
Product Type	18MM STD Ind Prox 2W Ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113743240
Manufacturers Part Number	E57LBL18A2E
UPC	782113743240

Taxonomies, Classifications, and Categories

Category Description	SENSORS
igcc	6156
Type	E57
unspsc code	41111926

Packaging

Carton	1
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Automation And Logic Control Equipment
environmental conditions	NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
standard	UL Listed; CSA Certified
Temperature Rating	-13 to 158 F



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57LBL18A2E

UPC:782113743240

Dimensions:

- Height: .71 IN
- Length: 2.6 IN
- Width: .71 IN

Weight:.7 LB

Warranties:

- 1 year

Specifications:

- Type: E57
- Accuracy: <3% sensing range
- Contact Rating: 250 mA at 250V
- Cable Type: PVC
- Contact Configuration: 2-wire AC, NC
- Cord Length: 79.2 FT
- Enclosure Material: 303 stainless steel
- Environmental Rating: NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- Input Voltage: 20-250V
- Led Indicators: 360° viewable LED
- Maximum Ac Current: 250 mA
- Operating Mode: Unshielded
- Operating Temperature: -13° to 158°F (-25° to 70°C)
- Temperature Rating: -13° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LBL18A2E](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



