



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Inductive Proximity Sensor

E57LBL18A2E

UPC:782113743240

### Dimensions:

- Height: .71 IN
- Length: 2.6 IN
- Width: .71 IN

Weight:.7 LB

### Warranties:

- 1 year

### Specifications:

- Type: E57
- Accuracy: <3% sensing range
- Contact Rating: 250 mA at 250V
- Cable Type: PVC
- Contact Configuration: 2-wire AC, NC
- Cord Length: 79.2 FT
- Enclosure Material: 303 stainless steel
- Environmental Rating: NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- Input Voltage: 20-250V
- Led Indicators: 360° viewable LED
- Maximum Ac Current: 250 mA
- Operating Mode: Unshielded
- Operating Temperature: -13° to 158°F (-25° to 70°C)
- Temperature Rating: -13° to 158°F

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LBL18A2E](#)

### Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



