

Eaton E75-PP1MP-M12

Catalog Number: E75-PP1MP-M12

Eaton 20 Series Self Contained Metal Body Photoelectric Sensor Replacement Cover, Photoelectric, Right Angle, Die Cast Aluminum enclosure

General specifications



Product Name	Catalog Number
Eaton E75 IntelliView photoelectric sensor	E75-PP1MP-M12
	UPC
	786685262420
Product Length/Depth	Product Height
1.97 in	2.6 in
Product Width	Product Weight
0.9 in	0.2 lb
Warranty	Compliances
3 year	Contact Manufacturer

defaultTaxonomyAttributeLabel

Contact Rating

100 mA at 10-30 Vdc

Enclosure material

ABS

Operating mode

Background suppression

Connection

M12

Contact configuration

Complementary PNP open collector

Series

E75

Sensor type

Back ground suppression

Input voltage

10-30 Vdc

LED indicator

Stability: green

Output: yellow

Number of pins

4

Maximum DC current

100 mA

Operating temperature - max

131 °F

Operating temperature - min

-13 °F

Environmental rating

IP67

Resources

Brochures

[Introducing IntelliView](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E75-PP1MP-M12](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)