

Specifications



Eaton EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover
CATALOG NUMBER	EABC26
UPC	782274247809
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.78 in
PRODUCT WEIGHT	4 lb
PRODUCT TYPE	Conduit outlet box with cover

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 4 7 9

Resources

CATALOGS	Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page
CERTIFICATION REPORTS	Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification (EAB) Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification (EAB)
INSTALLATION INSTRUCTIONS	IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes IF 1472 - EAB Condulet Conduit Outlet Bodies
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - EABC26
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart

Product specifications

SHAPE	C
TRADE SIZE	3/4"
COVER OPENING DIAMETER	3"
MATERIAL	Feraloy iron alloy

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

