

Specifications

Eaton EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover
CATALOG NUMBER	EABC26
UPC	782274247809
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.78 in
PRODUCT WEIGHT	4 lb
PRODUCT TYPE	Conduit outlet box with cover



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

STANDARDS TYPE NEC/CEC

NEC HAZARDOUS RATING Class I, Division 1
Class I, Division 2
Class II, Division 1
Class II, Division 2
Class III

NEMA RATING 3
4
7
9

Resources

CATALOGS [Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

CERTIFICATION REPORTS [Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)
[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

INSTALLATION INSTRUCTIONS [IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - EABC26](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

Product specifications

SHAPE C

TRADE SIZE 3/4"

COVER OPENING DIAMETER 3"

MATERIAL Feraloy iron alloy

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

