

# Eaton EABX16 SA

Catalog Number: EABX16 SA

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Copper-free aluminum, X shape, 1/2"

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABX16 SA
	<b>UPC</b>
	782274945392
<b>Product Length/Depth</b>	<b>Product Height</b>
5.31 in	5.31 in
<b>Product Width</b>	<b>Product Weight</b>
2.53 in	1.9 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

X

### Trade size

1/2"

### Cover opening diameter

3"

### Material

Copper-free aluminum

## Resources

### Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

### Specifications and datasheets

[Eaton Specification Sheet - EABX16 SA](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)