

# Eaton EABX26

Catalog Number: EABX26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, X shape, 3/4"

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>   | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series Condulet<br>EAB conduit outlet box with cover | EABX26                |
|   | <b>UPC</b>            |
|   | 782274248707          |
| <b>Product Length/Depth</b>   | <b>Product Height</b> |
| 5.56 in   | 5.56 in               |
| <b>Product Width</b>  | <b>Product Weight</b> |
| 2.78 in   | 4.86 lb               |

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

X

### Trade size

3/4"

### Cover opening diameter

3"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

### Specifications and datasheets

[Eaton Specification Sheet - EABX26](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)