

Eaton EABX36 SA

Catalog Number: EABX36 SA

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Copper-free aluminum, X shape, 1"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABX36 SA
	UPC
	782274945286
Product Length/Depth	Product Height
5.56 in	5.56 in
Product Width	Product Weight
2.78 in	1.5 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Shape

X

Trade size

1"

Cover opening diameter

3"

Material

Copper-free aluminum

Resources

Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

Specifications and datasheets

[Eaton Specification Sheet - EABX36 SA](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)