





Moeller SK0211-1149GB

	Inputs		Outputs			Additional features		Supply	Part number
	Digital	Useable as analog	Relay (8 amp.)	Transistor	Analog	Display & keypad	Real time clock		
Expandable base units (easy700)									
	12		6			✓	✓	110/240 V AC	EASY719-AC-RC
	12	4	6			✓	✓	24 V AC	EASY719-AB-RC
	12	4	6			✓	✓	24 V DC	EASY719-DC-RC
	12	4	6			✓	✓	12 V DC	EASY719-DA-RC
	12	4		8		✓	✓	24 V DC	EASY721-DC-TC
	12		6				✓	110/240 V AC	EASY719-AC-RCX
	12	4	6				✓	24 V AC	EASY719-AB-RCX
	12	4	6				✓	24 V DC	EASY719-DC-RCX
	12	4	6				✓	12 V DC	EASY719-DA-RCX
	12	4		8			✓	24 V DC	EASY721-DC-TCX
Expandable, networkable base units (easy800)									
	12		6			✓	✓	110/240 V AC	EASY819-AC-RC
	12	4	6			✓	✓	24 V DC	EASY819-DC-RC
	12	4			1	✓	✓	24 V DC	EASY820-DC-RC
	12	4		8		✓	✓	24 V DC	EASY821-DC-TC
	12	4		8	1	✓	✓	24 V DC	EASY822-DC-TC
	12		6				✓	110/240 V AC	EASY819-AC-RCX
	12	4	6				✓	24 V DC	EASY819-DC-RCX
	12	4			1		✓	24 V DC	EASY820-DC-RCX
	12	4		8			✓	24 V DC	EASY821-DC-TCX
	12	4		8	1		✓	24 V DC	EASY822-DC-TCX
Expansion units (for easy700, easy800)									
	12		6					110/240 V AC	EASY618-AC-RE
	12		6					24 V DC	EASY618-DC-RE
	12			8				24 V DC	EASY620-DC-TE
			2						EASY202-RE



Moeller SK0211-1149GB

