


## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5150 N. Hwy 81 73533-0000, OK Duncan Phone: 580-252-2582 Fax: 580-252-2738





**Category Description** 

Type

## EC0101 3/4" Weatherhead Appleton/Oz Gedney

EC0101 Appleton/Oz Gedney
Appleton/Oz Gedney
Features: 3.64IN Depth X 2.8IN Height, (2) 3/8 In, (3) 13/32 In
Holes, Weather Resistant, For Threaded/Unthreaded Rigid
Conduit, Imc/Emt Service Masts, Standard:UI 514B, Nema FB-1,
Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
0.2900 (lbs/each)
Service Entrance CBL Fittings
Die Cast Zinc
Unfinished
0.75
3/4" WEATHERHEAD
EGS ECO-101 3/4 IN ALUM CLP ON ENTR
Features: 3.64IN Depth X 2.8IN Height, (2) 3/8 IN, (3) 13/32 IN
Holes, Weather Resistant, For Threaded/Unthreaded Rigid
Conduit, IMC/EMT Service Masts, Standard:UL 514B, NEMA FB-1
Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
3/4 In Alum CLP On Entr Cap
3.64 IN Depth X 2.8 IN Height, (2) 3/8 IN, (3) 13/32 IN Holes,
Weather Resistant, For Threaded/Unthreaded Rigid Conduit,
IMC/EMT Service Masts
Appleton
00687855251018
ECO-101
687855251018

Fittings & Ground Rods Clamp-On Entrance Cap

SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding



## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5150 N. Hwy 81 73533-0000, OK Duncan Phone: 580-252-2582 Fax: 580-252-2738

Packaging	
Carton	10
Package	50
Weight Per each	0.29
Uses, Certifications, and Standards	
Application	Clamp on Type For Use With Threaded or Unthreaded EMT or
	IMC Conduit
standard	UL 514B, NEMA FB-1