

# Eaton ECC03C1A3A

Catalog Number: ECC03C1A3A

Eaton C30CN mechanically held lighting contactor, 30 A, 110 V/50 Hz, 120 V/60 Hz, 30 A, NEMA 1, Painted steel, Three-pole, Electrically held, C30CN Series, Non-combination electrically and mechanically held



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton C30CN mechanically held lighting contactor	ECC03C1A3A
	<b>UPC</b>
	782116154203
<b>Product Length/Depth</b>	<b>Product Height</b>
7.62 in	12.6 in
<b>Product Width</b>	<b>Product Weight</b>
6 in	13 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	cUL Listed

## Catalog Notes

Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

## defaultTaxonomyAttributeLabel

### Accessories

ON/OFF pushbutton

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Type

Non-combination electrically and mechanically held

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact rating

30 A

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Operation

Electrically held

### Series

C30CN

## Resources

### Brochures

[Lighting contactors](#)

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECC03C1A3A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)