

Eaton ECC03C2A6A

Catalog Number: ECC03C2A6A

Eaton C30CN mechanically held lighting contactor, 30 A, 110 V/50 Hz, 120 V/60 Hz, 30 A, NEMA 3R, Painted steel, Six-pole, Electrically held, C30CN Series, Non-combination electrically and mechanically held



Photo is representative

General specifications

Product Name	Catalog Number
Eaton C30CN mechanically held lighting contactor	ECC03C2A6A
	UPC
	782116162574
Product Length/Depth	Product Height
8.625 in	15.875 in
Product Width	Product Weight
8.375 in	20 lb
Warranty	Certifications
1 year	cUL Listed
	UL Listed

Catalog Notes

Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

defaultTaxonomyAttributeLabel

Accessories

ON/OFF pushbutton

Amperage Rating

30A

Number Of Poles

Six-pole

Type

Non-combination electrically and mechanically held

Coil voltage

110-120 Vac, 50/60 Hz

Contact rating

30 A

Enclosure

NEMA 3R

Enclosure material

Painted steel

Operation

Electrically held

Series

C30CN

Resources

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECC03C2A6A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)