

Eaton ECC04C1ABA

Catalog Number: ECC04C1ABA

Eaton C30CN mechanically held lighting contactor, 30 A, 110 V/50 Hz, 120 V/60 Hz, 30 A, NEMA 1, Painted steel, 12-pole, MECH held and MAG latched, C30CN Series, Non-combination electrically and mechanically held



Photo is representative

General specifications

Product Name	Catalog Number
Eaton C30CN mechanically held lighting contactor	ECC04C1ABA
	UPC
	782116157082
Product Length/Depth	Product Height
7.62 in	12.6 in
Product Width	Product Weight
6 in	13 lb
Warranty	Certifications
1 year	UL Listed
	cUL Listed

Catalog Notes

Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

12-pole

Type

Non-combination electrically and mechanically held

Coil voltage

110-120 Vac, 50/60 Hz

Contact rating

30 A

Enclosure

NEMA 1

Enclosure material

Painted steel

Number of wires

3

Operation

Mechanically held, magnetically latched

Series

C30CN

Resources

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECC04C1ABA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

