



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **ECL03A1A3A LTG Eh 10A Encl 1 120V 3P**

*Eaton Corp*

|                  |                                                                                                                                                                        |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | ECL03A1A3A                                                                                                                                                             |
| Manufacturer     | Eaton Corp                                                                                                                                                             |
| Description      | CN35 or A202 Enclosed Lighting Contactor, Non-Combination Electrically Held, 10A, Painted Steel Nema 1 Enclosure, 110V/50 HZ, 120V/60 HZ Coil, Three-Pole, 45 MM Frame |
| Weight per unit  | 5.2 (lbs/each)                                                                                                                                                         |
| Product Category | Lighting Contactors                                                                                                                                                    |

### **Features**

|                |                                   |
|----------------|-----------------------------------|
| Coil Voltage   | 110-120 Vac, 50/60 Hz             |
| dimensions     | 5.6200 IN X 5.7100 IN X 9.5100 IN |
| Enclosure Type | Nema 1                            |
| media          | Yes                               |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | LTG EH 10A ENCL 1 120V 3P                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| extra long description | ETN ECL03A1A3A LTG EH 10A ENCL 1 12                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Features               | Type CN35 electrically held lighting contactors are designed to handle the switching of tungsten (incandescent) or ballast (fluorescent and mercury arc) lamp loads as well as other non-motor (resistive) loads. Ideal applications include industrial plants, stadiums, parks and any new construction requiring lighting control. Ballast lamps equate to fluorescent, mercury vapor, sodium vapor and quartz loads and will operate at a maximum of 600V. Filament lamps equate to incandescent, infrared, sodium iodine an |
| Long Description       | CN35 or A202 Enclosed Lighting Contactor, Non-combination electrically held, 10A, Painted steel NEMA 1 enclosure, 110V/50 Hz, 120V/60 Hz coil, Three-pole, 45 mm frame                                                                                                                                                                                                                                                                                                                                                          |
| Product Type           | LTG Eh 10A Encl 1 120V 3P                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782114189849 |
| Manufacturers Part Number | ECL03A1A3A     |
| UPC                       | 782114189849   |

### **Taxonomies, Classifications, and Categories**

|                      |                                      |
|----------------------|--------------------------------------|
| Category Description | ENCLOSED                             |
| Type                 | Electrically held lighting contactor |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 5.2 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                                                                                                                                                                                                  |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsElec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - OtherElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsInd Facilities & Factories - Facility: Lighting and Lighting Controls |
| standard    | cUL Listed,UL Listed                                                                                                                                                                                                                                                                                                                                                                                             |