

Eaton ECL03B1A4A

Catalog Number: ECL03B1A4A

Eaton CN35 electrically held lighting contactor, 20 A, 120 V/60 Hz, 110 V/50 Hz, 20 A, NEMA 1, Painted steel, 45 mm, Four-pole, A202 Series, Contactor



Photo is representative

General specifications

Product Name

Eaton CN35 electrically held lighting contactor

Catalog Number

ECL03B1A4A

UPC

782114152676

Product Length/Depth

7.73 in

Product Height

12.6 in

Product Width

5.84 in

Product Weight

5.2 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

OSHPD Certified
ABS Certified
cUL Listed

Catalog Notes

C30CN available in 30A only

defaultTaxonomyAttributeLabel

Amperage Rating

20A

Number Of Poles

Five-pole

Type

Lighting contactors

Coil voltage

110-120 Vac, 50/60 Hz

Contact rating

20 A

Enclosure

NEMA 1

Enclosure material

Painted steel

Frame size

45 mm

Series

A202

Resources

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Eaton Specification Sheet - ECL03B1A4A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)