

Specifications

Eaton 84-29237-41

Eaton CN35 electrically held lighting contactor, HAND/OFF/AUTO selector switch, 30 A, 120 V/60 Hz, 110 V/50 Hz, 30 A, NEMA 1, Four-pole, A202 Series, Lighting contactors

General specifications

PRODUCT NAME	Eaton CN35 electrically held lighting contactor
CATALOG NUMBER	84-29237-41
UPC	782114078068
PRODUCT LENGTH/DEPTH	7.73 in
PRODUCT HEIGHT	13.21 in
PRODUCT WIDTH	5.84 in
PRODUCT WEIGHT	12.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	OSHPD Certified UL Listed ABS Certified cUL Listed
CATALOG NOTES	C30CN available in 30A only



Powering Business Worldwide

Product specifications

AMPERAGE RATING	20A
NUMBER OF POLES	Six-pole
TYPE	Non-combination electrically held
ACTUATOR	HAND/OFF/AUTO selector switch
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT RATING	20 A
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Painted steel
OPERATION	Electrically held
SERIES	A202

Resources

MULTIMEDIA	S1. E4. Ask the Experts - NEMA, IEC and DP contactors
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 84-29237-41

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

