



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723



ECN5542CAHR63F PP 150A HMCP N3R SZ4 480V CL

Eaton Corp

Catalog Number	ECN5542CAHR63F
Manufacturer	Eaton Corp
Description	Eaton Freedom Industrial Pump Panel, Circuit Breaker Disconnect, Nema 3R Painted Steel Enclosure, 440V/50 HZ-460V/60 HZ Coil, Nema Size 4, 28-140A Solid-State Relay Without Ground Fault, 150A Breaker
Weight per unit	120.0 (lbs/each)
Product Category	Nema Combination Starters

Features

Coil Voltage	440V/50 Hz-460V/60 Hz
--------------	-----------------------

Dimensions and Weight

Depth	50
Height	12.5
Size	NEMA size 4
Width	23

Descriptions

Description	PP 150A HMCP N3R SZ4 480V CL
extra long description	ETN ECN5542CAH-R63/F PP 150A HMCP N
Features	Eaton's industrial pump panels are combination starters that are designed for irrigation, oil well, gas and other pump applications. The enclosure is NEMA Type 3R to provide weather-tight protection and is available in several sizes, depending on the customer's control option requirements. The disconnect, contactor and overload relay are the same as used in Freedom lines of combination starters.
Long Description	Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 4, 28-140A solid-state relay without ground fault, 150A breaker
Product Type	PP 150A HMCP N3R SZ4 480V CL

Manufacturer Information

Brand	Eaton Corp
GTIN	00786685456324
Manufacturers Part Number	ECN5542CAH-R63/F
UPC	786685456324

Packaging

Carton	1
Weight Per each	120



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Industrial Facilities/Factories -
Other Stationary Machinery and Equipment Outside Factory -
Pumps and Compressors

standard

UL Listed, cUL Listed, OSHPD Certified