

Eaton ECNR30

Catalog Number: ECNR30

Eaton Edison ECNR fuse, Time-delay current-limiting fuse, Superior overload and cycling capabilities, 30 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 200 kAIC, Standard, 250 V, 125 Vdc

General specifications

Product Name	Catalog Number
Eaton Edison ECNR fuse	ECNR30
UPC	Product Length/Depth
782634507345	8.5 in
Product Height	Product Width
2.35 in	2.35 in
Product Weight	Warranty
1.84 lb	Not Applicable
Compliances	
CE Marked	



Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Fuse indicator

Non-indicating

Special features

Non current limiting

Resources

Catalogs

[Edison full line catalog 1005](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - ECNR30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia