# U-Line® Factory Sealed 15 and 20 Amp Plugs 🗐

## **Explosionproof, Dust-Ignitionproof**

These watertight plugs also fit NEMA 5-15R, 5-20R or 6-20R receptacles in nonclassified areas. Choice of Aluminum or Thermoplastic Polyester Plug.

Class I, Division 1 and 2 Groups B, C, D Class II, Division 1 and 2 Group G and Coal Dust Class III CSA Type 7BCD, 9G

### **Applications**

- U-Line® Interchanger™ ECP plug: suitable for use in such areas as refineries, petrochemical plants, and other areas subject to where ignitable gases are present.
- NCP Plug: ideal where moisture or corrosion is a constant problem, such as production facilities on marine platforms, and pipeline transportation facilities.

#### **Features**

- Unique blade-type, brass contacts exert constant pressure along entire contact surface and provide superior electrical contact.
- Insulators provide superior dielectric and mechanical strength and lowest arc tracking.
- Longer plug housing for better gripping and easier plug insertion and withdrawal.


- Plugs fits any standard non-explosionproof receptacle (NEMA 5-15R, 5-20R, or 6-20R) as well as U-Line explosionproof receptacles.
- 15 Amp ECP1523 125 Vac and 20 Amp ECP2023 125 Vac U-Line plugs are for use in the T-slot configured 20 Amp U-Line receptacle. ie ECSK-2023.
- ECP plug: a twist of the plug produces audible "click" to indicate fast make and break of built-in switch contacts.
  Twisting plug locks it in place and cannot be accidentally pulled out.
- NCP plug: special neoprene watertight plug bushing accommodates flexible cord ranging from .538" to .639" diameter.

#### **Standard Materials**

- ECP plug: copperfree (less than 4/10ths of 1%) aluminum
- NCP plug: 30% glass-reinforced thermoplastic polyester

					Catalog Number	
	Amp	Diagram	Wire/ Pole	Cable Dia., (Inches)	125 Vac	250 Vac
U-Line <sup>®</sup> Interchanger™ ECF	• Standard Plug	1				
_	15	<u>(1)</u>	2W, 3P	.538 to .639	ECP-1523	
	20	<b>(-1)</b>	2W, 3P	.538 to .639	ECP-2023	
	20	•	2W, 3P	.538 to .639		ECP-20232
NCP Plug						
	15	$\bigcirc$	2W, 3P	.538 to .639	NCP-1523	
「「「「」」	20	<u>.</u>	2W, 3P	.538 to .639	NCP-2023	
	20	<u>•</u>	2W, 3P	.538 to .639		NCP-20232

#### **Dimensions**





M CSA Certification only.