

Eaton ECS98V2CAH-C1P7S3

Catalog Number: ECS98V2CAH-C1P7S3

Eaton S611 soft starter, Combination reduced voltage, circuit breaker, Standard size CPT, 110V/50 Hz, 120V/60 Hz secondary with fuses, NEMA 3R enclosure, START/STOP, HAND-OFF-AUTO selector switch, 150A breaker, 99A, 460V

General specifications



Photo is representative

Product Name

Eaton S611 soft starter

UPC

786685620695

Product Height

8.75 in

Product Weight

150 lb

Certifications

UL Listed

cUL Listed

Catalog Number

ECS98V2CAH-C1P7S3

Product Length/Depth

35 in

Product Width

29.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Coil voltage

120V/60 Hz

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Combination reduced voltage

Accessories

110V/50 Hz, 120V/60 Hz secondary with fuses

Actuator

START/STOP, HAND-OFF-AUTO selector switch

Amperage Rating

99A

Circuit breaker rating

150A

Control power transformer voltage

120 Vac, 480 Vac

Size

99A max RVSS

Special features

Standard size control power transformer

Style

Circuit breaker

Voltage rating

460 V

Resources

Brochures

[Enclosed S611 solid-state soft starter](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Multimedia

[Soft starter DS7 up to 200 A](#)

[Soft Starter DS7 up to 32 A](#)

[Soft Starter Product Family Overview](#)

Specifications and datasheets

[Eaton Specification Sheet - ECS98V2CAH-C1P7S3](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)