

# Eaton ECS98Y2CAJ-C1P7S3

Catalog Number: ECS98Y2CAJ-C1P7S3

Eaton S611 soft starter, NEMA 3R, 200A/600V R disconnect fuse, START/STOP, HAND-OFF-AUTO selector SW, 250A breaker, 180A, 460V

## General specifications



Photo is representative

### Product Name

Eaton S611 soft starter

### UPC

786685620749

### Product Height

10.68 in

### Product Weight

180 lb

### Certifications

UL Listed

cUL Listed

### Catalog Number

ECS98Y2CAJ-C1P7S3

### Product Length/Depth

61.75 in

### Product Width

28 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## defaultTaxonomyAttributeLabel

### Coil voltage

120V/60 Hz

### Enclosure

NEMA 3R

### Enclosure material

Painted steel

### Type

Combination reduced voltage

### Accessories

110V/50 Hz, 120V/60 Hz secondary with fuses

### Actuator

START/STOP, HAND-OFF-AUTO selector switch

### Amperage Rating

180A

### Circuit breaker rating

250A

### Control power transformer voltage

120 Vac, 480 Vac

### Size

180A max RVSS

### Special features

Standard size control power transformer

### Style

Circuit breaker

### Voltage rating

460 V

## Resources

### Brochures

[Enclosed S611 solid-state soft starter](#)

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Multimedia

[Soft starter DS7 up to 200 A](#)

[Soft Starter DS7 up to 32 A](#)

[Soft Starter Product Family Overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECS98Y2CAJ-C1P7S3](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)