

Specifications

Photo is representative

Eaton EGH3015FFG

Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 15 A, 600Y/347 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, 35 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz

General specifications

PRODUCT NAME	Eaton Series G complete molded case circuit breaker
CATALOG NUMBER	EGH3015FFG
UPC	782116131204
PRODUCT LENGTH/DEPTH	2.99 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC Rated CSA Certified UL Listed
PRODUCT TYPE	Molded case circuit breaker



Powering Business Worldwide

Product specifications

AMPERAGE RATING	15 A
VOLTAGE RATING	600Y/347 Vac
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	EG
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series G
TERMINALS	Line and load
FRAME	EG
FREQUENCY RATING	50/60 Hz
INTERRUPT RATING	35 kAIC at 600Y/347 Vac 65 kAIC at 480 Vac 100 kAIC at 240 Vac
NUMBER OF POLES	Three-pole
TYPE	Complete breaker

Resources

APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Series G MCCB quick selector](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Comprehensive circuit protection for control panel applications](#)

BROCHURES

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[StrandAble terminals product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Motor protection circuit breakers product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - EGH3015FFG](#)

[NG and ND-Frame molded case circuit breakers](#)

[MOEM MCCB product selection guide](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

