



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EGL24L197840HIAS Egl24l197840hiasslatch3wm

H.E. Williams, Inc.

Catalog Number	EGL24L197840HIAS
Manufacturer	H.E. Williams, Inc.
Description	Led Enclosed High Bay, 19700 LM (Frosted Lens);19800 LM (Clear Lens) Brightness (Lumens), 82 Color Rendering Index, 5000 K Color Temperature, Led Enclosed High Bay Fixture Type, Ceiling Mount Bracket;Stainless Steel Mounting Strap Includes, IP65;IP66;IP67 Ip Rating, Led Lamp Type, 4 FT Length, Made In Usa, Acrylic;Aluminum;Stainless Steel (V-Hook, Latch) Material, Ceiling Mount;Surface Mount, Flame and Weather Resistance;Liquid-Tight Power Entry Special Features, Cetlul Listed;DLC Listed;NSF/Ansi Standard
Weight per unit	23.0 (lbs/each)
Product Category	Led Highbay Lighting

Descriptions

Description	EGL24L197840HIASSLATCH3WM
-------------	---------------------------

Manufacturer Information

Manufacturers Part Number	EGL2-4-L197/840-HIA-3WMR-DRV-U
---------------------------	--------------------------------

Taxonomies, Classifications, and Categories

Category Description	LED HIGH ABUSE, WET LOCATION, CLEAN ROOM & MEDICAL LIGHTING
----------------------	---

Packaging

Carton	1
Weight Per each	23