ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

EI500WC Digital 7DAY Timer WH

Intermatic Inc.

Catalog Number	EI500WC
Manufacturer	Intermatic Inc.
Description	Timer, 24 H Time Setting Mode, 1 No Contact Form, 125 V Ac, 15 A, 1 Pole, Light Almond (Wall Plate), +32 °F Operating Temperature, +122 °F Operating Temperature, 1.4375 X 1.75 X 4.125 In Size, 2.5 LB
Weight per unit	0.2500 (lbs/each)
Product Category	Electronic Time Switches

Features

action	1 x SPST
amperage rating	15
Contact Configuration	1 NO
Contact Rating	15 AMP @ 120 VAC (Resistive Heater), 8.3 AMP @ 120 VAC (Tungsten Incandescent), 8 AMP @ 120 VAC (Ballast Magnetic)
motor power	1/4 HP @ 120 VAC
Poles	1
Timing Range	1 MIN - 7 DAYS
Wattage	1,875

Descriptions

Description	DIGITAL 7DAY TIMER WH
extra long description	INT-MAT EI500WC 7-Day Standard Prog

Manufacturer Information

GTIN	00078275105232
UPC	078275105232

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Decorator Digital In-Wall

Packaging

Carton	1
Package	6
Weight Per each	0.25

Uses, Certifications, and Standards

Frequency Rating	60
Mounting	WALL MOUNT
Operating Temperature	+32 to +122 DEG F, 0 to +50 DEG C
standard	cULus Listed, HVACR