

Eaton EIBB

Catalog Number: EIBB

Eaton Crouse-Hinds series EIB circuit breaker enclosure, 40A through 100A, Without circuit breaker, Bolted/ground joint cover construction, Copper-free aluminum

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series EIB circuit breaker enclosure	EIBB
	UPC
	782274288857
Product Length/Depth	Product Height
12.53 in	16.53 in
Product Width	Product Weight
9.75 in	61.5 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class III

NEMA Rating

3

3R

4

7

9

Product specifications

Enclosure

Without circuit breaker

Amperage Rating

40 A through 100 A

Enclosure cover construction

Bolted/ground joint

Enclosure material

Copper-free aluminum

Resources

3D models

[SP3D Design Package - EIB Explosionproof Compact Circuit Breakers](#)

Brochures

[EIB Series Explosionproof Compact Circuit Breakers flyer](#)

Catalogs

[EIB Series Explosionproof Compact Circuit Breakers catalog page](#)

Certification reports

[EIB Explosionproof Compact Circuit Breakers UL certification](#)

[EIB Explosionproof Compact Circuit Breakers Canadian certification](#)

Installation instructions

[IF 1501 - EIB Series Circuit Breakers and Enclosures](#)

Specifications and datasheets

[Eaton Specification Sheet - EIBB](#)