





The EID Disconnect Switch provides an explosion proof disconnect with overload and circuit protection for hazardous area electrical systems. This disconnect solution incorporates Eaton's Crouse-Hinds' high integrity manufacturing standards for safety and reliability in a compact, space-efficient NEMA 4X† enclosure.

Features and Benefits:

- Available in both fused and non-fused configurations offers flexible options for different circuit protections
- Can be ordered as enclosure only allows for field installation of switch while maintaining product certification
- NEMA 4X breather and drain* provides a moisture control solution in hose-down applications
- Small, compact footprint less mounting space required
- Large red painted aluminum rotary handle operator mounted on cover assembly — provides rugged, reliable performance in the field and allows for the switch position to be easily identified
- Internal fused switches are rated up to 200kAIC short circuit rating at 600 VAC, providing increased protection
- Neoprene cover gasket provides NEMA 4 ingress protection
- Detachable/adjustable mounting feet provides flexible mounting alternatives for ease of installation; no need to replace the entire enclosure if a mounting foot is broken
- Stainless steel hinges easy internal access for wiring and maintenance
- (2) ½" NPT conduit entries, one on top and one on bottom for field addition of breather and/or drain or for use with auxiliary contacts; holes come plugged with Eaton's Crouse-Hinds PLG explosionproof plug as standard**
- Provides lockout/tagout capability which complies with OSHA requirements — allows for locking in the ON or OFF position for standard maintenance checks
- Complies with NEC Article 312 wire bending requirements for maximum wire gauge — allows for easy and safe installation, and reliable operation of the product

Certifications and Compliances:

- Class I, Divisions 1 & 2, Groups B, C, D
- Class I. Zones 1 & 2
- Class II, Division 1, Groups E, F, G
- Class III
- NEMA 3, 3R, 4, 4X†, 7BCD, 9EFG
- UL Standard: 1203
- cUL to CSA C22.2 No. 30



Standard Materials:

- Body and cover copper-free aluminum
- Gasket neoprene
- Cover bolts steel, stainless steel†
- Hinges stainless steel
- Mounting plate sheet aluminum
- Rotary actuating handle aluminum

Standard Finishes:

- Copper-free aluminum natural
- Steel electrogalvanized

Electrical Ratings:

Non-fused	Horsepower Rating			Fused Horsepower Rating					
Switch Rating (Amps)	240 VAC	480 VAC	600 VAC	250 VDC	Switch Rating (Amps)	240 VAC	480 VAC	600 VAC	250 VDC
30	10	20	30	5	30	-	15	20	5
60	20	40	40	10	60	-	30	50	10
100	30	50	50	20	100	-	60	75	20
200	75	150	200	15	200	60	125	150	40
400	125	250	350	50	400	125	250	350	50

^{*}When ordered with S756V suffix.

^{**}For both drains and auxiliary contacts, please contact factory.

tWhen ordered with S752 or S753 suffix.

Ordering Information:

Jiueinig iiii	Enclosure with			
Amperage	Fused/Non-fused	Enclosure Only	Switch	
30	Non-fused	EIDA	EIDA3030	
30	Fused	EIDAF3	EIDAF3030	
60	Non-fused	EIDA	EIDA3060	
60	Fused	EIDAF6	EIDAF3060	
100	Non-fused	EIDB	EIDB3100	
100	Fused	EIDBF	EIDBF3100	
200	Non-fused	EIDC	EIDC3200	
200	Fused	EIDCF	EIDCF3200	
400	Non-fused	EIDD	EIDD3400	
400	Fused	EIDDF	EIDDF3400	

Options:


		<u>Suffix</u>
•	Auxiliary contact (single block)	S784
•	Auxiliary contacts (two blocks)	S785
•	Breather and drain	S756V
•	Epoxy powder coat finish (external only)	S752
•	Epoxy powder coat finish (internal and external)	S753
•	External ground lug	S214

Dimensions and Weights:


NON-FUSED EID

Dimension	EIDA	EIDB	EIDC	EIDD
A	9.65"	11.75"	13.19"	13.49"
	(245mm)	(298mm)	(335mm)	(343mm)
В	5.00"	7.00"	14.94"	14.94"
	(127mm)	(178mm)	(380mm)	(380mm)
С	10.47"	12.53"	17.44"	17.19"
	(266mm)	(318mm)	(443mm)	(437mm)
D	11.13"	15.13"	17.50"	29.50"
	(283mm)	(384mm)	(445mm)	(749mm)
E	12.47"	16.53"	29.44"	41.22"
	(317mm)	(420mm)	(748mm)	(1047mm)
F	2.75"	2.75"	5.00"	5.00"
	(70mm)	(70mm)	(127mm)	(127mm)
Weights	36 lbs.	62 lbs.	167 lbs.	258 lbs.
	(16 kg.)	(28 kg.)	(76 kg.)	(117 kg.)
Conduit Size (Top & Bottom)	1.0"	1.5"	3.0"	(2) 3.0"






EIDA/EIDB




EIDC/EIDD

FUSED EID

Dimension	EIDAF3	EIDAF6	EIDBF	EIDCF	EIDDF
A	10.02"	9.90"	10.05"	13.19"	13.49"
	(255mm)	(251mm)	(255mm)	(335mm)	(343mm)
В	7.00"	7.00"	14.94"	14.94"	14.94"
	(178mm)	(178mm)	(380mm)	(380mm)	(380mm)
С	12.67"	12.53"	17.31"	17.44"	17.19"
	(322mm)	(318mm)	(440mm)	(443mm)	(437mm)
D	13.13"	15.13"	11.50"	17.50"	29.50"
	(333mm)	(384mm)	(292mm)	(445mm)	(749mm)
E	14.67"	16.53"	23.31"	29.44"	41.22"
	(373mm)	(420mm)	(592mm)	(748mm)	(1047mm)
F	3.50"	3.50"	3.50"	5.00"	5.00"
	(89mm)	(89mm)	(89mm)	(127mm)	(127mm)
Weights	47 lbs.	51 lbs.	108 lbs.	180 lbs.	271 lbs.
	(21 kg.)	(23 kg.)	(49 kg.)	(81 kg.)	(123 kg.)
Conduit Size (Top & Bottom)	1.5"	2.0"	2.5"	3.0"	(2) 3.0"





U.S. (Global Headquarters): **Eaton's Crouse-Hinds Business**

1201 Wolf Street Syracuse, NY 13208

(866) 764-5454 FAX: (315) 477-5179 FAX Orders Only: (866) 653-0640

CrouseCustomerCTR@ Eaton.com

www.crouse-hinds.com

For more information:

If further assistance is required, please contact an authorized Eaton Distributor, Sales Office, or Customer Service Department.

Canada

Toll Free: 800-265-0502 FAX: (800) 263-9504

FAX Orders only: (866) 653-0645

Mexico/Latin America/Caribbean:

52-555-804-4000 FAX: 52-555-804-4020 ventascentromex@eaton.com

Europe (Germany)

49 (0) 6271 806-500 49 (0) 6271 806-476 sales.CCH.de@ cooperindustries.com

Middle East (Dubai)

971 4 4272500 FAX: 971 4 4298521 sales.CCH.me@ cooperindustries.com

Singapore

65-6645-9888 FAX: 65-6297-4819 chsi-sales@ cooperindustries.com

China

86-21-2899-3600 FAX: 86-21-2899-4055 cchsales@ cooperindustries.com

Korea

82-2-3484-6783 82-2-3484-6778 CCHK-sales@ cooperindustries.com

Australia

61-2-8787-2777 FAX: 61-2-9609-2342 CEASales@ cooperindustries.com

India

91-124-4683888 FAX: 91-124-4683899 cchindia@ cooperindustries.com

1000 Eaton Boulevard Cleveland, OH 44122 United States

Eaton's Crouse-Hinds Business

1201 Wolf Street Syracuse, NY 13208

© 2014 Eaton All Rights Reserved Printed in USA Publication No. 5102-0816 August 2016

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

