

Eaton EL29

Catalog Number: EL29

Eaton Crouse-Hinds series EL elbow, Female, Feraloy iron alloy or ductile iron, 90°, 3/4"

General specifications



| | |
|------------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series EL elbow | EL29 |
| UPC | Product Length/Depth |
| 782274307305 | 1.5 in |
| Product Height | Product Width |
| 2.5 in | 2.5 in |
| Product Weight | |
| 0.67 lb | |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Gender

Female

Material

Feraloy iron alloy

Ductile iron

Shape

90° angle

Trade size

3/4"

Resources

Catalogs

[Crouse-Hinds series Explosionproof Conduit Unions, Elbows and Tees catalog page](#)

Certification reports

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - EL29](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)