# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## EM3590 3/4 HP 1075 RPM 3 SPD 230V Blower MTR Shaft 1/2"X4

*Precision Electric Motor*

| | |
|---|---|
| Catalog Number | EM3590 |
| Manufacturer | Precision Electric Motor |
| Description | 60 Hertz Frequency Rating; Ul, Csa Approval; Direct Drive Fan and Blower Application; 208 to 230 Volt Ac 1-Phase Voltage Rating; Resilient Ring, Extended Stud Mounting; 18 Pound Weight; 3/4 HP Power Rating; 1075 RPM Speed Rating; Oao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 5.1/4.2/3.1 Amp Motor Fla; Yes Reversible; 3 Speed(S); 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Flat; Orientation Horizontal; Bearing T |
| Weight per unit | 18.0 (lbs/each) |
| Product Category | 20190723150534 |

## Descriptions

| | |
|---|---|
| Description | 3/4 HP 1075 RPM 3 SPD 230V BLOWER MTR SHAFT 1/2"X4 |
| Long Description | 60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; DIRECT DRIVE FAN AND BLOWER APPLICATION; 208 TO 230 VOLT AC 1-PHASE VOLTAGE RATING; RESILIENT RING, EXTENDED STUD MOUNTING; 18 POUND WEIGHT; 3/4 HP POWER RATING; 1075 RPM SPEED RATING; OAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 5.1/4.2/3.1 AMP MOTOR FLA; YES REVERSIBLE; 3 SPEED(S); 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE FLAT; ORIENTATION HORIZONTAL; BEARING T |
| Product Type | Motor Fan Blade |

## Manufacturer Information

| | |
|---|---|
| Brand | |
| GTIN | 00786674019530 |
| Manufacturers Part Number | 4VEA010 |
| UPC | 786674019530 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Generic HAVCR Motors |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 18 |