



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3615T 5HP 1755RPM 3PH 60HZ 184T 3642M Tefc F1 Motor

Baldor/Abb Motors & Mechanical

Catalog Number	EM3615T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Phase: 3 PH; Voltage Rating: 208-230/460 Vac; Horsepower: 5 HP; Speed Rating: 1750 RPM; Frequency Rating: 60 HZ; Full Load Current: 13.9-13.4/6.7 Amp; Torque Rating: 14.9 LB-FT Full Load, 52.2 LB-FT Break Down, 31.5 LB-FT Pull-U
Weight per unit	93.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	184 W
horsepower	5 in
Insulation Class	F
Phase	3 in
Power Factor	0.78 W
Service Factor	1.15 in
Speed Rating	1,750 rpm
Voltage Rating	208/230/460 V

Descriptions

Description	5HP 1755RPM 3PH 60HZ 184T 3642M TEFC F1 MOTOR
extra long description	BALDOR EM3615T 5HP,1750RPM,3PH,60HZ
Long Description	Baldor Electric; AC Motor; Phase: 3 PH; Voltage Rating: 208-230/460 VAC; Horsepower: 5 HP; Speed Rating: 1750 RPM; Frequency Rating: 60 HZ; Full Load Current: 13.9-13.4/6.7 AMP; Torque Rating: 14.9 LB-FT Full Load, 52.2 LB-FT Break Down, 31.5 LB-FT Pull-U
Product Type	5HP, 1750RPM, 3PH, 60HZ, 184T, 3642M, Tefc, F1
Special Features	5HP,1750RPM,3PH,60HZ,184T,3642M,TEFC,F1

Manufacturer Information

Brand	Baldor/Abb Motors & Mechanical
GTIN	00781568138991
Manufacturers Part Number	EM3615T
sub brand	Super-E
UPC	781568138991

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	93

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1