



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EM3774T 10HP 1765RPM 3PH 60HZ 215T 0748M Tefc F1

*Baldor/Abb Motors & Mechanical*

Catalog Number	EM3774T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Temperature Rating: 40 Deg C Amabient Condition; Horsepower: 10 HP; Phase: 3 PH; Voltage Rating: 230/460 Vac; Full Load Current: 24.4/12.2 Amp; Power Factor: 83; Service Factor: 1.15; Enclosure: Tefc; Frame: 215T; Insulation Cla
Weight per unit	191.0 (lbs/each)
Product Category	Motors

### Features

Base	Rigid
frame	215 W
horsepower	10 ft
Insulation Class	F
Phase	3 in
Power Factor	0.83 in
Service Factor	1.15 lb
Speed Rating	1,760 rpm
Voltage Rating	230/460 V

### Descriptions

Description	10HP 1765RPM 3PH 60HZ 215T 0748M TEFC F1
extra long description	BALDOR EM3774T 10HP,1760RPM,3PH,60H
Long Description	Baldor Electric; AC Motor; Temperature Rating: 40 DEG C Amabient Condition; Horsepower: 10 HP; Phase: 3 PH; Voltage Rating: 230/460 VAC; Full Load Current: 24.4/12.2 AMP; Power Factor: 83; Service Factor: 1.15; Enclosure: TEFC; Frame: 215T; Insulation Cla
Product Type	10HP, 1760RPM, 3PH, 60HZ, 215T, 0748M, Tefc, F1
Special Features	10HP,1760RPM,3PH,60HZ,215T,0748M,TEFC,F1

### Manufacturer Information

Brand	BALDOR
GTIN	00781568102855
Manufacturers Part Number	EM3774T
sub brand	Super-E
UPC	781568102855

### Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	191

## Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1