



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMT390 3", 90D Emt Elb

Robroy/Ecn Korns

Catalog Number	EMT390
Manufacturer	Robroy/Ecn Korns
Description	Emt Standard Radius Elbow, 3 In Trade Size, Galvanized, 90 ° Connection Orientation, 13 In Bend Radius, Threaded Connection, 720 LB/100
Weight per unit	7.2 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.3
Bend Angle	90 Degree
End Type	THREADED

Descriptions

Also Known As...	Sweep Elbow Pre-Fab
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	3",90D EMT ELB
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; ZINC ELECTROPLATED FINISH; UL 797, UL (CANADA AND US), CSA C22.2, CAN/CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC 358, ISO 9001 APPLICABLE STANDARD; 3 INCH TRADE SIZE; PLAIN END TYPE; 90 DEGREE BEND ANGLE; 13 INCH BEND RADIUS; PACKAGING TYPE BULK; EMT ELB MODEL

Manufacturer Information

Brand	EC-KORNS
GTIN	00784011020287
Model	EMTELB
UPC	784011020287

Taxonomies, Classifications, and Categories

Category Description	EMT ELBOWS
Type	STANDARD RADIUS

Packaging

Carton	1
Standard Package	BULK
Weight Per each	7.1999

Uses, Certifications, and Standards

Approval	UL 797, CSA C22.2
----------	-------------------