



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMTELB2X90 2", 90D Emt Elb

Robroy/Ecn Korns

Catalog Number	EMTELB2X90
Manufacturer	Robroy/Ecn Korns
Description	Elbow, Standard Radius Type; UI 797, Csa C22.2 Approval; Ansi C80.3 Applicable Standard; 10 Per Carton Standard Package; 2 Inch Trade Size; Threaded End Type; 90 Degree Bend Angle; 9.5 Inch Bend Radius; Emtelb Model
Weight per unit	2.9 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.3
Bend Angle	90 Degree
Bend Radius	9.5 INCH
End Type	THREADED

Descriptions

Also Known As...	Elbow Pre-Fab Sweep
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	2",90D EMT ELB
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; ZINC ELECTROPLATED FINISH; UL 797, UL (CANADA AND US), CSA C22.2, CAN/CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC 358, ISO 9001 APPLICABLE STANDARD; 10 PER CARTON STANDARD PACKAGE; 2 INCH TRADE SIZE; PLAIN END TYPE; 90 DEGREE BEND ANGLE; 9.5 INCH BEND RADIUS; EMTELB MODEL
Long Description	ELBOW, STANDARD RADIUS TYPE; UL 797, CSA C22.2 APPROVAL; ANSI C80.3 APPLICABLE STANDARD; 10 PER CARTON STANDARD PACKAGE; 2 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 9.5 INCH BEND RADIUS; EMTELB MODEL
Product Type	Elbow

Manufacturer Information

Brand	ECN-KORNS
GTIN	00784011020263
Manufacturers Part Number	EMTELB2X90
Model	EMTELB
UPC	784011020263



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description EMT ELBOWS

Type STANDARD RADIUS

Trade Size

Trade Size 2 INCH

Packaging

Carton 1

Package 10

Standard Package 10 PER CARTON

Weight Per each 2.86

Uses, Certifications, and Standards

Approval UL 797, CSA C22.2