On-Q
14-inch Enclosure with Hinged Door
Part No. EN1450



MADE IN USA

This 14"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

- 14-in Enclosure with Hinged Door
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Made in the USA
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Cover included

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023036	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Cable Entry	(6) rear knockouts
Frame	Cold Rolled Steel		

On-Q
14-inch Enclosure with Hinged Door
Part No. EN1450



MADE IN USA

This 14"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

- 14-in Enclosure with Hinged Door
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Made in the USA
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Cover included

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023036	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Cable Entry	(6) rear knockouts
Frame	Cold Rolled Steel		