



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EN1450 14" Enclosure W/Hinged Cover + Lock

Pass & Seymour/Legrand

Catalog Number	EN1450
Manufacturer	Pass & Seymour/Legrand
Description	<P>This 14"" Enclosure Features Universal On-Q Bay-Style Mounting Holes That Are Compatible With All Bay-Style Modules. It Also Includes Larger Top Openings That Make Pulling Wire Easier As Well As Additional Knockouts, More Side Lances, and Side Tabs For
Weight per unit	9.8 (lbs/each)
Product Category	Enclosures & Cabinets

Features

Cable Entry	(6) rear knockouts
Enclosure Size	14.0
face plate	Hinged Cover and Lock
frame	Cold Rolled Steel
Material	Steel

Material, Color, and Finish

Color	White
Finish	Powder Coat

Dimensions and Weight

Depth	3.7"
Height	14.1"
Thickness	0.1
Width	14.3"

Descriptions

Description	14" ENCLOSURE W/HINGED COVER + LOCK
extra long description	OnQ EN1450 14 ENCL W/HINGED COVER +
Long Description	<p>This 14"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for
Product Type	14 Encl W/Hinged Cover + Lock
Special Features	Flanged covers hide drywall openings- Flush and surface-mounted- Mounting tabs provide correct flush-mount position



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428023036
Manufacturers Part Number	EN1450
UPC	804428023036

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	ENCLOSURE

Packaging

Carton	1
Weight Per each	9.75

Uses, Certifications, and Standards

Application	Residential
Mounting	Surface or Flush
standard	UL, ROHS, CULUS, CSA, UL (UL985, UL1023, UL1863), cULus, CSA, RoHS