



On-Q
14-inch Enclosure with Hinged Door
Part No. EN1450



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

14-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023036	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Additional Information

RoHS Compliant

Yes

Technical Information

Thickness

0.1 in

Cable Entry

(6) rear knockouts

Frame

Cold Rolled Steel
