

ENCLOSURES

Standard Enclosures

EN2000

20" Enclosure with Screw-On Cover



EN2000

20" ENCLOSURE WITH SCREW-ON COVER

This 20 inch enclosure includes a mounting hole pattern that supports both traditional and bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a screw-on cover.

PART NO.	DESCRIPTION
EN2050	20" Enclosure With Hinged Door
EN2080	20" Enclosure (no cover)
EN2060	20" Hinged Door
EN2020	20" Screw-On Cover
EN2085	20" Enclosure with Knockouts (no cover)

Notes: 20" H x 14.25" W x 3.6" D

EN2850

28" Enclosure with Hinged Door



EN2850

28" ENCLOSURE WITH HINGED DOOR

This 28 inch enclosure ships with a hinged, locking door, and is compatible with both traditional and bay style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, side lances, and side tabs for more flexible mounting.

PART NO.	DESCRIPTION
EN2800	28" Enclosure With Screw-On Cover
EN2880	28" Enclosure (no cover)
EN2860	28" Hinged Door
EN2820	28" Screw-On Cover
EN2885	28" Enclosure with Knockouts (no cover)

Notes: 28" H x 14.25" W x 3.6" D