



**On-Q**  
**20-inch Enclosure with Screw-On Cover**  
Part No. EN2000



This 20" enclosure universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flex

## Features & Benefits

20-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Cover included

Made in the USA

## Specifications

### General Info

|              |  |                    |               |
|--------------|--|--------------------|---------------|
| Product Line | On-Q   | Color              | White         |
| UPC Number   | 804428023067                                 | Country Of Origin  | United States |
| Material     | Steel  | Application Sector | Residential   |
| Standard     | UL (UL985, UL1023, UL1863), cULus, CSA, RoHS | Type               | Enclosure     |

### Dimensions

|                   |          |                  |        |
|-------------------|----------|------------------|--------|
| Product Width US  | 14.25 in | Product Depth US | 3.6 in |
| Product Height US | 20.0 in  | Enclosure Size   | 20 in  |

---

## Listing Agencies / 3rd Party Agencies

---

|            |     |              |     |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

---

## Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|           |        |             |                   |
|-----------|--------|-------------|-------------------|
| Thickness | 0.1 in | Cable Entry | (3) top knockouts |
|-----------|--------|-------------|-------------------|

---

|       |                   |
|-------|-------------------|
| Frame | Cold Rolled Steel |
|-------|-------------------|

---